

Certificate of Quality

The Polyethersulfone membrane filters have been manufactured in a **mdi** facility in compliance with **ISO 9001** regulations using **validated production processes**.

AseptiCap KS Polyethersulfone Membrane Filter

Catalog No. : IKS10636MHXX104
Type : IKS
Pore Size : 0.1 μm (0.2 μm + 0.1 μm)
Lot Number : IK9964H
Manufacturing Date : 2024 - 08
Expiry Date : 2029 - 08

SPECIFICATION

Membrane : Polyethersulfone
Housing : Polypropylene
Filter Diameter : 25 mm
Effective Filtration Area (Nominal) : 5 cm²
Burst pressure : > 14 Kg/cm²

LOT RELEASE CRITERIA

100% Integrity Tested : The filters have been tested for integrity by Bubble Point Test using purified water. Bubble point was: \geq 65 psi (4.48 Bar)
Typical Water Flow Rate : 15 ml/min @ 0.70 kg/cm² @ 27 °C
Microbial Challenge Test : Retains $\geq 10^7$ organisms/cm² of *Acholeplasma laidlawii* (ATCC 23206).

VALIDATED FOR

Bubble point (50% IPA) : The filter is certified/validated for integrity by Bubble point test using 50% IPA/Water solution. Bubble point \geq 26 psi (1.79 Bar)
Bacterial Endotoxin : Aqueous extracts exhibit < 0.25 EU/mL as established by Limulus Amebocyte Lysate (LAL) test as per USP <85>.
Biosafety : Passes Biological Reactivity Tests, *In Vivo* for Class VI plastic as described in USP <88>.
Cytotoxicity : Passes Biological Reactivity Tests, *In Vitro* as described in USP <87>.
Indirect Food Additives : Passes as per FDA 21CFR 177.1520(a)1(i).
Particle Release : Passes test as per USP <788>, "Particulate matter in Injections".
Fiber Release : Complies with FDA 21CFR 210.3(b)(6).
Extractable : Within limits as specified in USP.
Oxidizable matter : Passes test as per USP.
Total Organic Carbon : Meets USP <643> limit of 500 ppb for total organic carbon after flushing specified volume of water for injection.
Conductivity : Meets USP <645> limit of 1.3 $\mu\text{S/cm}$ at 25 °C for water conductivity after flushing specified volume of water for injection.

PRECAUTIONS

1. During handling, avoid contamination of outlet.
2. If pressure required to maintain the required flow becomes too high, the filter unit should be changed.

CUSTOMER SUPPORT

mdi offers its unique interdisciplinary skills to provide solutions to specific problems. Please contact our factory or the local application specialist.

T. No.: COQ/ILF/006-03



Head of Quality Assurance

Issue Date: 26-Aug-2024

Advanced Microdevices Pvt. Ltd.
21, Industrial Area, Ambala Cantt, INDIA,
Tel: +91-171-2699290/ 2699274
Website: www.mdimembrane.com
Email: info@mdimembrane.com

An ISO 9001 Company