

# Certificate of Quality

The Microglassfiber filter has been manufactured in a **mdi** facility in compliance with **ISO 9001** regulations using **validated production processes**.

## **ClariCap GS Microglassfiber Filters**

Catalog No. : IGSX0641MNXX104  
Type : IGS  
Pore Size : 0.7  $\mu$ m  
Lot Number : IG8567G

### **SPECIFICATION**

Membrane : Microglassfiber  
Housing : Polypropylene  
Filter Diameter : 25 mm  
Effective Filtration Area (Nominal) : 5 cm<sup>2</sup>  
Burst pressure : > 14 Kg/cm<sup>2</sup>

### **LOT RELEASE CRITERIA**

**Integrity Tested** : Each lot has been sampled and tested for integrity after manufacture

**Water Flow Rate** :  $\geq$  300 ml/min @ 0.70 kg/cm<sup>2</sup> @ 27 °C

### **PRECAUTIONS**

1. During handling, avoid contamination of outlet.
2. If pressure required to maintain the required flow becomes too high, the filter unit should be changed.

### **CUSTOMER SUPPORT**

**mdi** offers its unique interdisciplinary skills to provide solutions to specific problems. Please contact our factory or the local application specialist.



Head of Quality Assurance

Issue Date: 24-Jul-17

**Advanced Microdevices Pvt. Ltd.**  
21, Industrial Area, Ambala Cantt, INDIA,  
Tel: +91-171-2699290/ 2699274  
Website: [www.mdimembrane.com](http://www.mdimembrane.com)  
Email: [info@mdimembrane.com](mailto:info@mdimembrane.com)

**An ISO 9001 Company**